

CUSTOM MODIFICATIONS


Why Take a Chance with Faulty Wiring and Inaccurate Drawings? Ask OMEGA to Do It ALL for You!

CUSTOM ENGINEERING LEVEL I



Pre-wired 483 mm (19") Panel with Switch and Meter Is Installed in Control Room.

Free Documentation Supplied for Client Proposal.



A CASE IN POINT

An independent engineering consultant working on a new control room for a client needs a subminiature Type K thermocouple panel with forty inputs, a rotary selector switch, and an OMEGA® DP41 digital panel meter.

PROBLEM

Though the consultant is confident that OMEGA can provide the quality instrumentation he requires for this project, he has two special requests. He wants the panel pre-wired because he does not have the time, the manpower, or the capability to do so, and he also would like a design drawing of the panel so he can incorporate it into the proposed plans for his client.

OMEGA® SOLUTION

Custom Engineering suggests a standard OMEGA® 19MJP-4-40-K-OSW-MTR panel with an OSW5-40 selector switch and the specified DP41 meter. All of the thermocouple jacks are pre-wired to the switch and meter, complete and ready for installation with computer-generated dimensional drawing.

ASK OMEGA TO PRE-WIRE YOUR NEXT PANEL!



PHONE, FAX OR E-MAIL WITH YOUR SPECIAL REQUESTS


1-800-82-66342
1-800-TC-OMEGA®

Custom Engineering Fax:

1-203-359-7890

e-mail Custom Engineering
custom@omega.com

... If You Don't See What You're Looking For, Ask Us!



Multiple Thermocouple Calibrations in the Same Panel Saves Control Room Space



Reduced Tip Bayonet to Fit Existing Fixture