

DC Powered DIN Rail 4 to 20 mA Signal Splitter



DRI-SP-DC



- ✓ Provides Two Fully Isolated 4 to 20 mA Outputs in Proportion to a Single 4 to 20 mA Input
- ✓ 2000 Vac Isolation
- ✓ High Density DIN Rail Mounting
- ✓ Universal DC Power 10.8 to 26.4 Vdc
- ✓ Plug-in Terminals



DRI-SP-DC shown smaller than actual size.

The model DRI-SP-DC is a DIN rail mount, 4 to 20 mA signal splitter, with 2000 Vac isolation between input, output and power. It provides two fully isolated 4 to 20 mA outputs in proportion to a single 4 to 20 mA input. Front accessed zero and span potentiometers allow 50% adjustment of offset and gain to compensate for sensor errors or signal losses.

The DRI-SP-DC features plug-in screw terminals for easy installation. Two or more modules can slide together and interlock for solid, high density mounting (remove either the DIN rail foot or the adjacent unit's faceplate, for right side or left side mounting, respectively). The module to be attached will easily slide onto the side of the mounted unit.

DC input four-wire transmitters are used to isolate and convert DC signals into proportional, standard industrial control signals. Typically an industrial control system such as a DCS or PLC requires standard industrial control signals with full isolation to ensure reliable, strong signals.

In most industrial process control or data acquisition applications, several different input sources from various field instruments (e.g. level, flow, pressure and position sensors), are common. Four-wire transmitters accept these field inputs and provide the controller (DCS & PLC) with the standard industrial signal it requires. The four-wire transmitter will increase the signal drive to high impedance loads and may improve resolution of the process variable. The DRI-SP-DC operates as a four-wire transmitter and derives its power from an independent, transformer isolated DC power source (10.8 to 26.4 Vdc).

Specifications

INPUT

Range: 4 to 20 mA

Impedance: $\leq 20 \Omega$

Protection: Withstands up to 24 Vdc without damage

Common Mode: 2000 Vac, input to ground

OUTPUT (2 CHANNELS)

Range: 4 to 20 mA

Current Output Compliance: 15V (750 Ω , max)

LED Indication: Green LED indicates power on

Output Accuracy:

$\leq \pm 0.1\%$ of full-scale input typical

$\leq \pm 0.2\%$ maximum @ 23°C including linearity, repeatability and hysteresis

Adjustability: Front accessed 10 turn pot, $\pm 50\%$ of range for zero and span

Stability: $\leq 0.025\%/^{\circ}\text{C}$ of full-scale maximum for full-scale and zero

Isolation: ≥ 2000 Vac between input and output and channel-to-channel

Response Time: 25 msec typical (10 to 90%)

Power: 10.8 to 26.4 Vdc, 2 W per channel max

Temperature:

Operating: -5 to 60°C (23 to 140°F)

Storage: -40 to 80°C (-40 to 176°F)


Humidity (Non-Condensing):

Operating: 15 to 90% RH @ 45°C (113°F)

Soak: 90% RH for 24 hours @ 60°C (140°F)

Wire Terminal: Socketed screw terminals for 12 to 22 AWG

Weight: 227 g (0.5 lb)



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

To Order	
Model No.	Description
DRI-SP-DC	DC powered DIN rail 4 to 20 mA signal splitter
RAIL-35-1	35 mm DIN rail, 1 m (3.3') length
RAIL-35-2	35 mm DIN rail, 2 m (6.6') length
DCPB-2	DC power distribution bus for 2 modules
DCPB-4	DC power distribution bus for 4 modules
DCPB-8	DC power distribution bus for 8 modules

Ordering Example: DRI-SP-DC, DC powered DIN rail 4 to 20 mA signal splitter, RAIL-35-1 35 mm DIN rail, 1 m (3.3') length, DCPB-2 DC power distribution bus for 2 signal conditioner modules and OCW-1 OMEGACARE extends standard 1-year warranty to a total of 2 years.