

# OM-40 Series Portable Low Cost Data Loggers Part of the NOMAD® Family

**\$65**

Basic Unit



- ✓ Measure and Record Temperature, Relative Humidity, DC Voltage or DC Current Input
- ✓ Stores up to 7943 Readings
- ✓ Compact Size
- ✓ Easy-to-Use Windows Software

The OM-40 Series data loggers can record temperature, relative humidity, 4 to 20 mA and 0 to 2.5 Vdc signals. Model OM-41 measures temperature only (internal temperature sensor). Model OM-42 is a two channel data logger that measures temperature (internal sensor) and also one external signal which can be an external temperature probe, 4 to 20 mA signal or 0 to 2.5 Vdc signal. Model OM-43 measures temperature and relative humidity (internal sensors). Model OM-44 is a four channel data logger that measures temperature and relative humidity (internal sensors) and also up to two external signals which can be external temperature probes, 4 to 20 mA signals or 0 to 2.5 Vdc signals.

The internal temperature sensor is on a 10.6 cm (4") wire which is mounted on the circuit board inside the snap lid of the data logger case. Typically this sensor is left inside the case and measures ambient air temperature over the operating temperature range of the logger -20 to 70°C (-4 to 158°F).

The internal temperature sensor can also be placed outside of the case, for faster response time. When the sensor is placed outside of the case it is capable of measuring temperatures from -40 to 120°C (-40 to 248°F).



OM-41 data logger, \$65, shown larger than actual size

## Specifications

### GENERAL

**Measurement Capacity:**

7943 readings

**Measurement Interval:** User

selectable from 0.5 sec to 9 hrs  
**Memory Modes:** Stop when full, wrap-around when full (user selectable)

**Memory:** Non-volatile EEPROM memory retains data even if battery fails

**Operation:** Blinking LED light confirms operation

**Time Accuracy:** ±1 minute per week at 20°C (68°F)

**Operating Temperature:** -20 to 70°C (-4 to 158°F)

**Operating Humidity:** 0 to 95% non-condensing

**Storage Temperature:** -20 to 70°C (-4 to 158°F)

**Power:** 3.0 V lithium battery (included)

**Battery Life:** 1 year

**Dimensions:**

68 H x 48 W x 19 mm D (2.4 x 1.9 x 0.8")


**Weight:** 29 g (1 oz)

## Measurement Specifications Temperature (internal sensor) - All Models

**Measurement Range:** Sensor inside case, -20 to 70°C (-4 to 158°F); sensor outside case, -40 to 120°C (-40 to 248°F)

**Sensor Type:** Thermistor

**Accuracy:** ±0.7°C @ 21°C (±1.27°F @ 70°F) (see plot)



Temperature Measurement Accuracy/Resolution

### Resolution:

0.4°C (0.7°F) at 70°F

### Response Time (Still Air):


15 min typical with sensor inside case; 1 min typical with sensor outside case

### Relative Humidity


(user-replaceable internal sensor) Models OM-43 and OM-44

### Measurement Range:

25 to 95% RH at 80°F for intervals of 10 seconds or greater, non-condensing and non-fogging (see plot)



Relative Humidity Measurement Range vs. Temperature



Windows Software-Data Plot.

Windows Software-Data logger Setup.



OM-44 data logger, \$109, shown smaller than actual size.



OM-43, \$99, data logger smaller than actual size.

**Sensor Type:** Resistive  
**Accuracy:**  $\pm 5\%$   
 5 to 50°C (41 to 122°F)  
**Resolution:** 0.4%  
 5 to 50°C (41 to 122°F)  
**Response Time:**  
 10 min typical in air

**External Temperature Sensors (for use with Models OM-42 and OM-44) Measurement Range:**

**OM-40-C-HT-B** (for use in water or soil): -40 to 50°C (-40 to 122°F)

**OM-40-C-HT-B** (for use in air): -40 to 100°C (-40 to 212°F)

**Sensor Type:** Thermistor  
**Input Connection:**  
 2.5 mm stereo phone jack

**External 4 to 20 mA Input (for use with Models OM-42 and OM-44) Measurement Range:** 0 to 20.1 mA

**Input Connection:**  
 2.5 mm stereo phone jack  
**Accuracy:**  $\pm 0.1$  mA  $\pm 1\%$  rdg  
**Resolution:** 0.4% of fs

**External 0 to 2.5 Vdc Input (for use with Models OM-42 and OM-44) Measurement Range:** 0 to 2.5 Vdc

**Input Connection:**  
 2.5 mm stereo phone jack; external input ground, input, switched 2.5 V output; external input ground connection is not the same as PC interface connection ground and should not be connected to any external ground  
**Input Impedance:** 10 k $\Omega$   
**Accuracy:**  $\pm 10$  mV  $\pm 1\%$  rdg  
**Resolution:** 10 mV (8-bit)  
**Output Power:** 2.5 Vdc at 2 mA, active only during measurements

**ALL MODELS AVAILABLE FOR FAST DELIVERY!**

**To Order (Specify Model Number)**

Model No.	Price	Description
OM-41	\$65	Temperature data logger
OM-42	72	Temperature/external input data logger (takes one external input)
OM-43	99	Temperature/relative humidity data logger
OM-44	109	Temperature/relative humidity/external input data logger (takes up to two external inputs)
OM-40-C-HT-B	39	External temperature sensor for use with Models OM-42 and OM-44 (high temperature range, for use in air or water) 1.8 m (6') cable
OM-40-C-V	11	External 0 to 2.5 Vdc voltage input cable for use with Models OM-42 and OM-44
OM-40-C-I	19	External 4 to 20 mA input cable for use with Models OM-42 and OM-44
RD-TEMP-SW-A	59	Windows 98/NT/2000/XP software and RS-232 interface cable with DB9F termination for OM-40 Series data loggers
OM-40-BATT-6	20	Replacement 3.0 V lithium battery for OM-40 Series data loggers (package of 6)

Data loggers are supplied with complete operator's manual and mounting kit (hook/loop, magnet and tape).

**Ordering Example:** OM-44 data logger, OM-40-C-HT-B external temperature sensor, OM-40-C-V voltage input cable, and RD-TEMP-SW-A Windows software, \$109 + 39 + 11 + 59 = \$218.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters