

OMB-DBK60 3-Slot Expansion Module with Termination Panels

\$649


Basic unit with one
Terminal Panel



- ✓ Customizable Panels Offer User Choice of Signal Connector Types
- ✓ Accepts up to Three OMB-DBK Analog Expansion Cards or Three OMB-DBK Digital Expansion Cards
- ✓ Enables Easy Card Installation
- ✓ Rugged All Metal Construction for Portable Applications
- ✓ Attaches to the OMB-LOGBOOK or OMB-DAQBOARD-2000 Series

The OMB-DBK60 expansion module allows the OMB-LOGBOOK and OMB-DAQBOARD-2000 Series data acquisition systems to be expanded with any combination of up to three analog or three digital OMB-DBK signal conditioning and expansion cards.

Removable termination panels offer the user a choice of connector types including BNC, removable screw terminal, thermocouple and safety jacks. Each panel includes pre-stripped wires by which the user can connect to any of the three OMB-DBK cards installed in the OMB-DBK60 enclosure. A user-customizable blank termination panel is also available for custom applications.




The OMB-DBK60, \$649, shown smaller than actual size

The OMB-DBK60, \$649, analog or digital expansion module may be customized with the user's choice of signal connectors


The OMB-DBK60's three-card internal backplane eases cabling by bringing all connections out to a single DB37, thus only a single cable is required to attach an OMB-DBK60 to a system. Analog and digital DBK cards cannot be mixed within one OMB-DBK60 enclosure, and thus a separate enclosure is required for analog or digital cards.

An unlimited number of OMB-DBK60 enclosures can be secured to one another or an OMB-LOGBOOK system. The OMB-DBK60's metal enclosure features a slide-in drawer for easy access to the OMB-DBK cards.


The OMB-DBK60 can be used as an expansion module for OMB-DAQBOARD-2000 Series systems. Each OMB-DBK60 will accept up to three analog expansion cards or three digital expansion cards. Analog and digital expansion cards cannot be mixed within one OMB-DBK60 enclosure.



BNC termination panel OMB-DBK602 features 16 BNC connectors




Removable-block screw-terminal termination panel (OMB-DBK606) offers 48 convenient connections




Safety-jack termination panel offers 16 connectors (OMB-DBK604, red and black jack-pairs shown)




Slotted panel with adjustable clamp that holds wires in place (OMB-DBK607)



Thermocouple termination panel (OMB-DBK605) features 14 connectors for types J, K, and T thermocouples



DB37-style termination panel (OMB-DBK608) features three standard 37-pin female connectors



The OMB-DBK60, \$649, shown smaller than actual size

Eight different termination panels are available for use with the OMB-DBK60. These include the OMB-DBK602 BNC termination panel, OMB-DBK603 red safety-jack termination panel, OMB-DBK604 red and black safety-jack panel, OMB-DBK605 thermocouple input termination panel (specify thermocouple type), OMB-DBK606 removable-block screw terminal panel, OMB-DBK607 slotted termination panel with adjustable clamp and OMB-DBK608 termination panel with three DB37 connectors. (See previous page).

Termination Panels

To complement OMB-DBK cards installed in the OMB-DBK60 enclosure, users have a choice of eight termination panels that provide a variety of input connectors. The termination panels screwmount to the rear of the OMB-DBK60 chassis, and include the appropriate style wire to connect each input to an enclosed OMB-DBK60.

Packaging

You can stack the OMB-DBK60 beneath an OMB-LOGBOOK portable acquisition module. The result is a compact and securely connected data acquisition system that you can conveniently carry from one application site to another.

Specifications

Capacity: Accommodates up to 3 OMB-DBK expansion cards; digital and analog OMB-DBK cards cannot be mixed within a single OMB-DBK60 enclosure

Material: Aluminum


Finish: Black, powder-coated

Dimensions: 280 x 356 x 89 mm (11 x 14 x 3.5")

Weight: 3.08 kg empty (7 lb); cards .25 to .75 kg each (8 to 12 oz)

The OMB-DBK60, \$649, drawer-style architecture with internal backplane simplifies the installation of up to 3 OMB-DBK signal-conditioning cards

Sample expansion systems for the OMB-DAQBOARD-2000 Series



The OMB-DBK60 expansion enclosures can house both analog and digital expansion cards in an OMB-LOGBOOK system, providing that analog and digital cards are in separate OMB-DBK60's.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
OMB-DBK60	\$649	3-slot expansion-card enclosure with 3 blank termination panels** and fastener panels

Ordering Example: OMB-DBK60 3-slot expansion card enclosure, OMEGACARESM 1-year extended warranty for OMB-DBK60 (adds 1 year to standard 1-year warranty), one OMB-DBK605-K type K thermocouple panel, one OMB-DBK606 screw terminal panel, and one OMB-DBK604 red and black safety jack panel, \$629 + 59 + 103 + 209 + 113 = \$1113.

Accessories and Cables

Model No.	Price	Description
OMB-DBK601	30	Blank termination panel
OMB-DBK602	124	16-connector BNC termination panel
OMB-DBK604	113	16-connector (8 pairs) red and black safety-jack termination panel and wiring kit
OMB-DBK605-(*)	103	14-connector thermocouple panel and wiring kit Thermocouple type B, J, K, R, S or T
OMB-DBK606	209	48-connector removable-block screw terminal panel and wiring kit
OMB-DBK607	51	Slotted-termination panel with adjustable clamp
OMB-DBK608	51	Three DB37 female connector termination panel and wiring kit
OMB-CA-37-1T	61	Expansion cable from OMB-LOGBOOK to similar width module, 2.5 in.
OMB-CA-37-3T	61	Expansion cable from OMB-LOGBOOK or OMB-DBK module to a single OMB-DBK60 directly below, 4.5 in
OMB-CA-37-4T	72	Expansion cable from OMB-LOGBOOK or OMB-DBK module to a single OMB-DBK60 directly below, 5.5 in
OMB-CA-37-8T	82	Expansion cable from OMB-LOGBOOK positioned more than one OMB-DBK60 height away from the appropriate P1 or P2 port, 11.5"

*Insert thermocouple type J, K, or T

**Blank termination panels are included at no charge when no additional panels are ordered.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters