

Thermocouple Data Loggers

OMYL-T15 and OMYL-T16



- ✓ Single Channel (OMYL-T15) or Dual Channel (OMYL-T16)
- ✓ User-Selectable for Type J, K, T, E, R, S, B, and N Thermocouples
- ✓ Up to 4 Million Readings (Internal Memory Size)
- ✓ Up to 4 Hz Sampling Rate
- High Accuracy
- ✓ 20 Bit A/D Converter
- Shock Proof, IP65 Housing (Dust and Water Jet Proof)
- ✓ Transfer Rate of 500 kbps
- **✓ Low Current Consumption**
- ✓ Up to 4 Years Battery Life

The OMYL-T15 single channel and OMYL-T16 dual channel thermocouple input data loggers are new low-cost battery powered thermocouple data loggers with integral reference junction which delivers accurate readings over a wide temperature range. These data loggers are fully user programmable for Types J, K, T, E, R, S, B and N thermocouples and are available with standard memory of 100,000 readings (OMYL-T15, OMYL-T16) or expanded memory of 4 million readings (OMYL-T15-4M, OMYL-T16-4M). These devices are programmable so that you can log data from either one or two channels.

The storage medium is non-volatile flash memory so no data is lost if the battery becomes discharged. Data logger setup as well as data retrieval is accomplished using the included standard OMYL-SOFT software. Downloaded data is stored in the OMYL-SOFT software as a text file for viewing in third party software packages or Microsoft Excel. The OMYL-SOFT standard software does not include any graphing functionality. Graphing and analyzing downloaded data files requires the OMYL-SOFT-PLUS version of the software (sold separately).



Thermocouple Types and Ranges

Thermocouple Types and hanges			
Type	Range	Resolution	Accuracy
J	-210 to 1200°C	0.022°C	0.6°C
	(-346 to 2192°F)	(0.039°F)	(1.08°F)
K	-200 to 1400°C	0.025°C	0.6°C
	(-328 to 2552°F)	(0.045°F)	(1.08°F)
T	-200 to 400°C	0.009°C	0.6°C
	(-328 to 752°F)	(0.016°F)	(1.08°F)
E	-200 to 1000°C	0.018°C	0.6°C
	(-328 to 1832°F)	(0.032°F)	(1.08°F)
R	-50 to 1750°C	0.028°C	0.6°C
	(-58 to 3182°F)	(0.050°F)	(1.08°F)
S	-50 to 1770°C	0.028°C	0.6°C
	(-58 to 3182°F)	(0.050°F)	(1.08°F)
В	250 to 1820°C	0.024°C	0.6°C
	(482 to 3308°F)	(0.043°F)	(1.08°F)
N	-200 to 1300°C	0.023°C	0.6°C
	(-328 to 2372°F)	(0.041°F)	(1.08°F)





OMYL-SOFT-PLUS graphical interface.

OMYL-T16 shown actual size.

SPECIFICATIONS

Number of Inputs

OMYL-T15/OMYL-T15-4M: Single channel OMYL-T16/OMYL-T16-4M: Dual channel

Thermocouple Connection: Female subminiature

(SMP) connector

Cold Junction Compensation: Automatic Reading Rate: 1 second to 24 hours; 2 Hz, 4 Hz

in fast mode

Start Modes: Immediate start, delayed start

Memory Capacity

OMYL-T15, OMYL-T16: 100,000 readings

OMYL-T15-4M, OMYL-T16-4M: 4 million readings **Memory Wrap Around:** Yes (software configurable) Battery: 3V lithium battery [standard temperature

range battery (included), optional high temperature range battery]; user replaceable

Battery Life (Standard Temperature Range Battery): 4 years at 1 minute reading rate, 230 days at 10 second

reading rate, 25 days at 1 second reading rate

LED Functionality: Integrated status LED indicates data logging status, low battery or alarm condition **Alarms:** Software programmable high/low thresholds Computer Interface: USB (interface cable included) Software: XP SP3/Vista/7 and 8 (32- and 64-bit) Operating Environment: -30 to 70°C (-22 to 158°F)

with standard lithium battery; -40 to 90°C (-40 to 194°F)

with optional high temperature lithium battery **Dimensions:** 45 H x 50 dia mm (1.77 x 1.97")

Weight: 70 a (2.5 oz)

Enclosure: Robust, shock-proof POM, IP65



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

To Order		
Model No.	Description	
OMYL-T15	Single channel thermocouple input data logger, 100,000 readings	
OMYL-T15-4M	Single channel thermocouple input data logger, 4 million readings	
OMYL-T16	Dual channel thermocouple input data logger, 100,000 readings	
OMYL-T16-4M	Dual channel thermocouple input data logger, 4 million readings	

Accessories

Model No.	Description	
OMYL-SOFT-PLUS	Plus version of the software for graphing and analyzing data files	
OMYL-WH20	Wall mount holder for data logger (includes tamper evident lead seal)	
OMYL-WS50	Set of 50 tamper evident lead seals (50 wires and 50 seals)	
OMYL-BATT	Replacement 3V lithium battery (standard temperature range)	
OMYL-BATT-HT	Replacement 3V lithium battery (high temperature range)	

Comes complete with 3V lithium battery (standard temperature range), 1.8 m (6') USB interface cable, OMYL-SOFT software and operator's manual on USB stick.

Ordering Example: OMYL-T15 single channel thermocouple input data logger, 100,000 readings and OCW-1, OMEGACARE ™ extends standard 1-year warranty to a total of 2 years.