

SS-001 Series

Wireless Smart Sensors with Cloud Connectivity



- **SS-001: Temperature, Humidity, Barometric Pressure, and Light sensors**
- **Free Layer N Standard Cloud service accessible from any connected device¹**
- **Easy setup with one-button pairing**
- **Transmits up to 1.2 km with standard AA batteries²**
- **Transmits up to 3.2 km when powered with USB²**
- **AES-256 Encrypted wireless link keeps your data secure**
- **Local data logging up to 10,649 data points³**



Layer N SS-001 Smart Sensors utilize precision internal sensing elements to accurately measure environmental conditions for a wide range of applications.

Long Range

The SS-001 utilizes Sub GHz Frequency Hopping Spread Spectrum (FHSS) technology to ensure robust, long range communications. Transmission ranges of up to 1.2 km can be achieved with the standard AA batteries and transmission ranges of up to 3.2 km can be achieved when powered by a standard 5V micro USB cable².

Advanced Features


Advanced Omega Level N features may be configured through SYNC software and include selective data extraction, measurement and device traceability, local alarms and adaptive transmission rates to reduce data congestion and extend battery life.

Plug and Play

Layer N Smart Sensors are easily paired to the Layer N Gateway with the press of a button, and will automatically show up on your Layer N Cloud Account. The Layer N Gateway can connect up to 256 Smart Sensors⁴ per unit. Local data logging keeps your data secure in the event of a power or network outage. Reports, History, and E-mail alerts from the Layer N Cloud keep you informed on the status of all your vital processes.

Secure

Layer N wireless products are designed with state of the art security features to protect your data with robust AES256 encryption and advanced PKA-EC521bit (NIST) elliptic-curve cryptography to protect your data.



1. Visit <https://omega.com/en-us/cloud> for subscription options. Total number of sensors that can connect to Layer N Cloud varies with subscription tier.

2. Actual range may vary depending on environment.

3. The number of data points available are on a per sensor basis. Local Data can be downloaded using downloadable SYNC configuration software.

4. 256 sensors are supported at typical update intervals, on the order of 60 minutes, higher data rates or adverse environmental conditions may diminish the number of sensors supported.

Specifications

Wireless Communication

Frequency: 915 MHz

Range: Up to 3.2 km*

*When powered by USB, without obstruction

Power

Alkaline Battery: 2x AA batteries (included)

Lifetime: Up to 1.5 years with frequency of 1 reading per hour

USB Power*: 500mA @ 5V

*Micro USB cable not included

Environmental

Operating Conditions for Base Unit

Battery Powered: -15°C to 55°C, non-condensing

USB Power: -20°C to 65°C, non-condensing

Rating: IP40


General

Software: Compatible with SYNC configuration software and Layer N Cloud

| Measurement | Range | Accuracy |
|----------------------------------|---------------------|---------------------|
| Temperature | -20°C to 70°C | ±0.3°C |
| Humidity @ 25°C | 0% to 80% | ±2.5% |
| | 80% to 100% | ±3.5% |
| Barometric Pressure @ 25°C | 700mbar to 1100mbar | ±4mbar |
| Barometric Pressure @ Full Range | 300mbar to 1100mbar | ±6mbar |
| Light | 0-43691 illuminance | Relative level only |

Your Data at a Glance with Layer N Cloud

Layer N Cloud consolidates and brings your data to you when you need it, wherever you are. The intuitive cloud interface allows you to monitor and store your data, set alarms and alerts, and provides insights on device activity.



Variants

The SS-001 is available in two variants of measurement suites: Temperature and Humidity or Temperature, Humidity, Barometric Pressure, and Light. Both operate on a frequency of 915 MHz

| Model Number | Description |
|--------------|---|
| SS-001-1-NA | Temperature and Humidity Smart Sensor - 915MHz |
| SS-001-3-NA | Temperature, Humidity, Barometric Pressure, Light Smart Sensor - 915MHz |

Gateway

A Wireless Gateway is **required** to connect the SS-001 to the Layer N Cloud. We currently offer the following options.

| Model Number | Description |
|--------------|--------------------------------|
| GW-001-0 | Wired IIoT Gateway Standard |
| GW-001-2-NA | Wireless IIoT Gateway Standard |
| GW-001-3-NA | Wireless IIoT Gateway Pro |