Paddle Flow Switch



FSW-160



- Multiple Quick-Change Paddles
- ✓ EPDM Seal
- ✓ Field Adjustable Set Points
- Direct Replacement for Most Paddle-Type Flow Switches
- High Flow Sensitivity
- Stainless Steel Paddles and Shaft
- ✓ NEMA 1 (IP10) Enclosure



The OMEGA® FSW-160 is the newest heavy-duty line of flow switches. The switch is used to signal, start, or stop electronically operated equipment when flow or no-flow conditions occur.

OMEGA's elastomeric sealing system is superior to the metal bellows that are subject to metal fatigue and corrosion. This seal system has been field-proven for over a decade. The FSW-160 can be used in pipes 1 inch and larger, with set-points as low as 4 GPM (15.2 LPM) to over 500 GPM (1893 LPM) in larger pipe sizes. The FSW160 uses a 15A SPDT micro switch that can control a ½ horsepower motor.

Specifications

Hysteresis (∆ Flow Rate to Activate/ Deactivate Switch)

10% at upper end of flow range 30% at lower end of flow range Differential Pressure Drops Across Unit Under Normal

Operating Conditions: 1 to 3" pipe, less than 1 psi

4 to 48" pipe, negligible Working Line Pressure:

200 psig maximum [proof tested to 1200 psig at 21°C (70°F)]

Working Temperature: 121°C (250°F)

maximum continuous
Wetted Materials:
Body and Lid: Brass

Shaft: 304 stainless steel Paddle: 316 stainless steel


Seal: EPDM

Electrical Switch Characteristics SPDT 15 A, ½ hp at 125 or 250 Vac 0.5 A at 125 Vdc (tungsten lamp) 0.25 A @ 250 Vdc (tungsten lamp)



Model Selection Chart

Flow Range [Water Calibrated at 21°C (70°F)]				
	Switchpoint Range (GPM)			
	Minimum Adjustment		Maximum Adjustment	
Pipe Size	On	Off	On	Off
1	4	2	8	7
1½	7	5	13	11
2	12	7	27	26
21/2	18	12	35	32
3	27	19	52	49
4	63	50	123	120
5	125	100	238	232
6	190	158	350	338



To Order	
Model No.	Description
FSW-160	Paddle flow switch brass 1 NPT, adjustable set-point

Comes complete with operator's manual.