
ULTRASONIC LEVEL TRANSMITTER AND CONTROLLER

LVCN318 Series



- Level Detection, Switch and Control Functions Up to 5.5 m (18')
- Fast and Easy Configuration Via Free Software Download and USB Adaptor
- Narrow 7.62 cm (3")
 Beam Width and Short
 20 cm (8") Dead Band
- ✓ Four Programmable Relays Range: 5.5 m (18)
- PVDF Transducer and 6P Polycarbonate Enclosure
- Automatic Temperature Compensation for Accurate Measurement

OMEGA's LVCN318 ultrasonic level transmitter and controller provides continuous level measurement up to 5.5 m (18') with a 4 to 20 mA signal output, and is configured via our free software download via a USB adaptor. The level sensor has 4 programmable relays with selectable hysteresis and fail-safe logic. The embedded level controller can lower cost by replacing external control hardware. This non-contact liquid level sensor is ideally suited for corrosive, sticky or dirty liquids, and is widely selected for day tank, skid, IBC, sump and process tank level applications.



SPECIFICATIONS

Range: 5.5 m (18') Accuracy: ±0.2% of range Resolution: 2 mm (0.079") Dead Band: 20 cm (8") Beam Width: 7.62 cm (3") Configuration: USB PC Windows®

USB 2.0 Memory: Non-volatile. The level sensor is configurable via our free PC software and USB adaptor. The sensors are offered with and without USB connectors. Connectors can be used to configure any compatible level product. Download your free copy at: omega.com/ftp Supply Voltage: 24 Vdc (loop) Consumption: 0.5W Loop Resistance: 400Ω maximum Signal Output: 4 to 20 mA, two-wire Signal Invert: 4 to 20 mA or 20 to 4 mA Signal Fail-Safe: 4 mA, 20 mA, 21 mA, 22 mA or hold last Contact Type: (4) SPST relays Contact Rating: 60 VA. 1A maximum Contact Fail-Safe: Power loss: hold last Echo Loss: Open, close or hold last Hysteresis: Selectable

Process Temperature: -7 to 60°C (20 to 140°F)

Temp Comp: Automatic Ambient Temperature: -35 to 60°C (-31 to 140°F) LVCN318.

Pressure: Maximum Working Pressure = 2 bar (30 psi) Enclosure Rating: Type 6P, encapsulated, corrosion resistant and submersible Encl Material: Polycarbonate Trans Material: PVDF Cable Jacket Material: Polyurethane Cable Type: 9-conductor, shielded Cable Length: 1.2 m (48") Process Mount: 2 NPT (2" G optional) Mount Gasket: FKM Classification: General purpose Compliance: CE, RoHS

To Order Visit omega.com/lvcn318 for Pricing and Details	
Model No.	Description
LVCN318	Level transmitter 4 to 20 mA and 4 relays, and USB connector, 5.5 m (18') range
LVCN318-B	Level transmitter 4 to 20 mA and 4 relays, 5.5 m (18') range (requires LVCN414-USB)
LVM31	Mounting reducer 1 Female NPT to 2 Male NPT
LVCN414-USB	USB connector (1 required for "-B" models, sold separately)

Comes complete with mounting gasket, software and operator's manual. For units with G threads add "-G" to model number, for additional cost. Configuration software for **programming available** free at **omega.com/ftp Ordering Example: LVCN318,** level transmitter with relays and USB connector, 2 NPT 5.5 m (18') range.