BATTERY-, LOOP-, AND AC-POWERED DIGITAL PRESSURE GAUGES DOMEGA

Three Power Options: Battery. Loop. or AC/DC



DPG1000 Series



- Vacuum to 5000 psi Ranges ✓ ±0.25% and ±0.10% Accuracy Models ✓ 316 SS Wetted Parts
- Loop Test Function
- Easy-to-Read 3½ Digit LCD
- Pressure or Vacuum Applications
- Rugged Aluminum or NEMA 4X (IP66) Case

The DPG1000 Series is a versatile family of industrial pressure/vacuum gauges. All DPG1000 models feature a large 13 mm ($\frac{1}{2}$) high digital display in a rugged, splashproof extruded aluminum case.

A ¼-18 NPT 316 stainless steel fitting is standard for the pressure connection. Media compatibility includes all liquids and gases compatible with 316 SS.

The DPG1000B Series features a wide operating temperature range of -20 to 85°C (-4 to 185°F). Many standard pressure/vacuum ranges (in a choice of engineering units) with both gauge and absolute references are available. The series also features $\pm 2x$ overpressure, and 4x burst specifications, and are available with either 0.25% or 0.10% accuracy.

DPG1000AD (AC/DC Powered)

The DPG1000AD is powered by either 8 to 24 Vac, or 9 to 32 Vdc. No recalibration is needed, and no jumpers have to be moved to use either AC or DC power within the specified range. No polarity needs to be observed when connecting a DC supply. Therefore, the DPG1000AD can be used with inexpensive, unregulated AC or DC power sources in applications requiring continuous pressure display.



shown smaller than actual size.

Backlit Display **Optional!**

> DPG1000B-300G shown smaller than actual size.

DPG1000B (Battery Powered)

The DPG1000B is powered by standard AA batteries that can operate the gauge for approximately 2500 hours. All DPG1000B models include a standard 5 minute auto shutoff feature to conserve battery life. Low-battery indication is also standard. An optional rubber boot (DPG1000-RB) is available. Requiring no electrical connection, the DPG1000B works equally well in portable or fixed applications.



(Loop Powered)

All operating power for the DPG1000L gauge is supplied by the 4 to 20 mA output loop. This "2-wire" connection lets the DPG1000L operate as a digital indicating transmitter in any 4 to 20 mA current loop application. Individual, noninteractive controls are available for the zero/span display and the output loop 4 to 20 mA settings. Connection to the DPG1000L is made via a 2-conductor cable at the back of the gauge.

A front-accessible TEST pushbutton switches the display and output loop to a preset level determined by the setting of a "Test Calibration" potentiometer. This feature allows easy testing of the display and process loop with a preset input signal in place of the actual input. The DPG1000L also includes "low loop" warning circuitry. This circuitry indicates on the display when the loop supply voltage falls below a level that may not be sufficient to drive a full 20 mA into the loop load resistance. These 2 proprietary features make the DPG1000L easier to set up and maintain.

DIGITAL PRESSURE GAUGES ±0.10 AND 0.25% ACCURACY MODELS



SPECIFICATIONS

Power: 2 "AA" batteries (included), provide

- B Models: Up to 2500 hr life typically; auto shut-off: 5 min; LOBAT indication
- **L Models:** 8 to 32 Vdc at gauge; reverse polarity protected **AD Models:** 8 to 24 Vac 50 to 60 Hz or 9 to 32 Vdc; 5 mA max

Pressure/Vacuum Reference:

Gage (psig) or absolute (psia)

Optional Units: Gauge can be factory scaled to any engineering unit such as psi, kPa, bar, mbar, inHg, inH₂O, mmHg, ftH₂O, torr, kg/cm²

Display Type/Size: LCD, 13 mm (0.5") digit height, 3 readings per second

Controls and Location:

B and AD models: Display zero/span, non-interactive, ±15% range; top-accessible, multiturn potentiometers **L Models:** Display zero/span, non-interactive, ±15% range; test calibration level, 0 to 100% range; topaccessible, multiturn potentiometers; loop 4 mA and 20 mA internal potentiometers

Accuracy:

DPG1000/1100: ±0.25% FSO or better, ±1 least significant digit (includes linearity, hysteresis, repeatability) **DPG1001:** ±0.10% FSO or better, ±1 least significant digit (includes linearity, hysteresis, repeatability)

Temperature Stability [25°C (77°F)]: DPG1000/1100: ±0.25% FSO or better, ±1 least significant digit (includes linearity, hysteresis, repeatability)±1% FS for offset and span, 0 to 70°C (32 to 158°F) typical; $\pm 2\%$ FS for offset and span, 0 to 70°C (32 to 158°F) typical for 3 and 5 psi range

DPG1001: ±0.003% FSO or better, ±1 least significant digit (includes linearity, hysteresis, repeatability); NIST traceable certificate included

Operating Temperature: -20 to 85°C (-4 to 185°F)

Compensated Temperature: 0 to 70°C (32 to 158°F)

Storage Temperature: -55 to 95°C (-67 to 203°F)

Weight: Approx. 255 g (9 oz)


Standard Case: Extruded aluminum case, epoxy powder coated; poly-carbonate cover, front and rear gaskets

NEMA 4X Case (DPG1100 models): UV stabilized polycarbonate/ABS case, clear polycarbonate window, gasketed rear cover, captive SS screws

Pressure/Vacuum Connection: 316 SS, ¼-18 MNPT Wetted Parts: 316 SS

Electrical Connection: 0.9 m (3') 2-conductor 22 AWG cable (none required on DPG1000B) Overpressure: 2x rated pressure min

Burst Pressure: 4x rated pressure min



Dimensions: mm (inch)

	W	Н	D
Std Case	86 (3.38)	73 (2.88)	42 (1.65)
NEMA 4X	89 (3.5)	76 (3.0)	51 (2.0)

OPTIONS

ORDER SUFFIX	DESCRIPTION	
-F10	10 min auto shut-off for DPG1000B units	
-F30	30 min auto shut-off for DPG1000B unit	
-NS	No auto shut-off for DPG1000B units	
BL	Backlit display*	

* Not available with DPG1000L models, with compound range "30V100G" models, or with DPG1001 models.

ACCESSORIES

MODEL NO.	DESCRIPTION
DPG1000-PS	Wall mount 115 Vac power supply for DPG1000AD units
DPG1000-RB	Rubber boot for DP1000B units

To Order					
RANGE (PSI)	±0.25% ACCURACY STANDARD CASE	±0.25% ACCURACY NEMA 4X CASE	±0.10% ACCURACY STANDARD CASE		
BATTERY POWERED	·	· · · · · · · · · · · · · · · · · · ·			
-30 inHg to 100.0	DPG1000B-30V100G	DPG1100B-30V100G	—		
0 to 5.00	DPG1000B-05G	DPG1100B-05G	DPG1001B-05G		
0 to 15.00	DPG1000B-15G	DPG1100B-15G	DPG1001B-15G		
0 to 30.0	DPG1000B-30G	DPG1100B-30G	_		
0 to 60.0	DPG1000B-60G	DPG1100B-60G	DPG1001B-60G		
0 to 100.0	DPG1000B-100G	DPG1100B-100G	DPG1001B-100G		
0 to 300	DPG1000B-300G	DPG1100B-300G	—		
0 to 500	DPG1000B-500G	DPG1100B-500G	DPG1001B-500G		
0 to 1000	DPG1000B-1KG	DPG1100B-1KG	DPG1001B-1KG		
0 to 2000	DPG1000B-2KG	DPG1100B-2KG	—		
0 to 3000	DPG1000B-3KG	—	_		
0 to 5000	DPG1000B-5KG	—	_		
LOOP POWERED-BACKL	IGHT NOT AVAILABLE				
0 to 5.00	DPG1000L-05G	DPG1100L-05G	DPG1001L-05G		
0 to 15.00	DPG1000L-15G	DPG1100L-15G	DPG1001L-15G		
0 to 30.0	DPG1000L-30G	DPG1100L-30G	—		
0 to 60.0	DPG1000L-60G	DPG1100L-60G	DPG1001L-60G		
0 to 100.0	DPG1000L-100G	DPG1100L-100G	DPG1001L-100G		
0 to 300	DPG1000L-300G	DPG1100L-300G	_		
0 to 500	DPG1000L-500G	DPG1100L-500G	DPG1001L-500G		
0 to 1000	DPG1000L-1KG	DPG1100L-1KG	DPG1001L-1KG		
0 to 2000	DPG1000L-2KG	DPG1100L-2KG	_		
0 to 3000	DPG1000L-3KG	_	—		
0 to 5000	DPG1000L-5KG	_	—		
AC/DC POWERED					
-30 inHg to 100.0	DPG1000AD-30V100G	DPG1100AD-30V100G	_		
0 to 5.00	DPG1000AD-05G	DPG1100AD-05G	DPG1001AD-05G		
0 to 15.00	DPG1000AD-15G	DPG1100AD-15G	DPG1001AD-15G		
0 to 30.0	DPG1000AD-30G	DPG1100AD-30G	_		
0 to 60.0	DPG1000AD-60G	DPG1100AD-60G	DPG1001AD-60G		
0 to 100.0	DPG1000AD-100G	DPG1100AD-100G	DPG1001AD-100G		
0 to 300	DPG1000AD-300G	DPG1100AD-300G	_		
0 to 500	DPG1000AD-500G	DPG1100AD-500G	DPG1001AD-500G		
0 to 1000	DPG1000AD-1KG	DPG1100AD-1KG	DPG1001AD-1KG		
0 to 2000	DPG1000AD-2KG	DPG1100AD-2KG	_		
0 to 3000	DPG1000AD-3KG	—	_		
0 to 5000	DPG1000AD-5KG		_		

Comes complete with operator's manual. DPG1001 models also include NIST-traceable calibration certificate.

15, 30 and 100 psi models available with absolute pressure range on DPG1000B models. Change model number from "-15G" to "-15A", "-30G" to "-30A", or "-100G" to "-100A", and add additional cost to price.
Ordering Examples: DPG1000B-100G, ±0.25% battery-powered digital gauge, 0 to 100.0 psig range. DPG1000BBL-60G, battery-powered ±0.25% unit, 60 psi range.

DPG1001L-500G, ±0.1% loop-powered digital gauge, 0 to 500 psig range.