
COMMERCIAL-GRADE GAUGES TYPE C


PGC Series



- ✓ Economically Priced
- ✓ Long-Lasting Movement
- ✓ Durable Construction
- Stocked Ranges for Fast Delivery

The OMEGA® spring-suspended movement represents the design of the future. Wearing parts have been reduced to a minimum. The entire movement is suspended between 2 springs, the Bourdon tube above and the link below. For the user, this means greater resistance to mechanical shock and vibration. This increased resistance to the effects of rough usage contributes to longer gauge life.





pressure gauges.

HOW TO ORDER COMMERCIAL GRADE GAUGES

Standard Case

The high reliability of the OMEGA® commercial gauge line is chiefly attributable to the unique OMEGA® spring-suspended movement. The entire movement is suspended between 2 springs, the Bourdon tube above and the link below. Wearing parts have been reduced to a minimum. Movement parts are ultrasonically cleaned and lubricated with silicone oil to ensure long cycle life. The OMEGA® springsuspended movement is largely resistant to shock, pulsation, and vibration. The result is longer gauge life. The numerous applications for OMEGA® commercial gauges include installation on pumps, portable compressors, industrial machinery, hydraulic and pneumatic systems, instrumentation, and pressurized vessels.

SPECIFICATIONS

Temperature: 66°C (150°F) maximum


Case: Painted steel


Window: Polycarbonate plastic Bourdon Tube: Bronze Connection: Brass ¼ NPT Ranges: Vacuum to 600 psi

Accuracy: 3-2-3% (3% over first and last 10% of range, 2% over remainder)

STANDARD RANGES

RANGE CODE	RANGE			
30V	30/0 inHg vac			
30V/15	30 inHg vac to 15 psi			
30V/30	30 inHg vac to 30 psi			
30V/100	30 inHg vac to 100 psi			
15	0 to 15 psi			
30	0 to 30 psi			
60	0 to 60 psi			
100	0 to 100 psi			
160	0 to 160 psi			
300	0 to 300 psi			
400	0 to 400 psi			
600	0 to 600 psi			





Dimensions: mm (inch)

DIAL		E			F						WT
SIZE	A	LOWER	BACK	С	NPT	G	Н	K	M	W	(OZ)
50.8 (2)	53 (2 ⁷ / ₆₄)	27 (1¾)	26 (1½)	54 (2 ⁷ / ₆₄)	1/4	47 (1 ²⁷ / ₃₂)	10 (%)	22 (%)	20 (²⁵ / ₃₂)	14 (%16)	4½
63.5 (2½)	69 (2 ²³ / ₃₂)	29 (1½)	29 (1½)	68 (2 ¹ 1/ ₁₆)	1/4	55 (2½)	10 (¾)	22 (%)	20 (²⁵ / ₃₂)	14 (%6)	6

To Order Visit omega.com/pgc for Pricing and Details					
DIAL SIZE	MODEL NO.	CONNECTION			
2"	PGC-20L-[*]	Lower			
	PGC-20B-[*]	Back			
2 ½"	PGC-25L-[*]	Lower			
	PGC-25B-[*]	Back			

[*] Insert range code from Standard Ranges table. Other standard ranges available; visit omega.com

Ordering Example: PGC-20B-30, commercial pressure gauge with 2" dial, back connection and 0/30 psi range.