2 m (6') integral USB cable connects

Metric threads and

ranges available.

# HIGH SPEED USB OUTPUT PRESSURE TRANSDUCER CONNECT DIRECTLY TO YOUR COMPUTER

Fast

Delivery!



PX409-015GUSBH

shown actual size.

**Gage and Absolute Pressures** 10 inH<sub>2</sub>O to 5000 psi (25 mb to 345 bar) **Vacuum and Compound Ranges** 10 inH<sub>2</sub>0 to 15 psi

**Barometric and Differential Pressure Ranges** 





- ✓ 1000 Readings/Second
- Micro-Machined Silicon Sensor
- ✓ 316L SS Wetted Parts
- ✓ High ±0.08% BSL Accuracy
- Excellent Long Term Stability
- ✓ USB 2.0 and Below Compatible
- Standard USB Connector Termination
- Shock and Vibration Rated
- Ruggedized with Secondary Containment

The PX409 High Speed USBH Series connects directly to your computer. Free PC software enables you to chart, log, display, and output data for analysis. Also included are .NET APIs, and a command set for command-line access. The micro-machined silicon design is ideal for pressure or level applications in laboratory, test platforms, or bio/pharmaceutical applications as well as industrial applications that require a rugged, high accuracy transducer. The micro-machined silicon sensor provides a very stable transducer with exceptional high accuracy of ±0.08% and a broad compensated range of -29 to 85°C (-20 to 185°F). The modular construction allows for fast delivery of most configurations and fittings. Delivery is typically stock to 1 week!

#### **SPECIFICATIONS**

Accuracy: 0.08% BSL (linearity, hysteresis

and repeatability combined)

**Resolution:** Up to 5.5 significant figures

**Temperature Compensation (Over Compensated Range):** 

Span: Range > 5 psi:  $\pm 0.5\%$ Range ≤ 5 psi: ±1.0% Zero: Range > 5 psi: ±0.5% **Range** ≤ 5 psi: ±1.0%

Minimum Isolation:

100 M $\Omega$  @ 50 Vdc case to sensor

2 M $\Omega$  @ 50 Vdc case to output terminations Pressure Cycles: 1 million, minimum

Long Term Stability (1-Year): ±0.1% full scale typical

A to D Conversion: 24-bit

Shock: 50 g, 11 mS half sine, vertical and horizontal axis

Vibration: 5-2000-5 Hz, 30 minute cycle, Curve L, Mil-Spec 810 figure 514-2-2,

vertical and horizontal axis

Bandwidth: DC to 1000 updates per second typical (±3%)

## directly to your PC. FREE OMEGA® USBH Downloadable Software!

OMEGA is excited to announce the release of a major software update for USB Transducers! The fresh look and added features add even more value and flexibility to your transducer's performance.

Free OMEGA PC software takes the data from the transducer directly to the digital domain, turning your laptop or Windows® tablet (with USB connection) into a virtual meter, chart recorder, or data logger.

Also included are .NET APIs and a set for command-line access. Visit ftp://ftp.omega.com/public/DASGroup/ products/USBH/ to download your free copy.\*

\*Includes software to run TRH Central compatible devices.

Power Consumption: 0.35 W typical **CE Compliant:** Meets industrial emissions and immunity EN61326

**Environmental Protection: IP65** Secondary Containment

Gage/Vacuum/Compound Pressure:

**10 inH<sub>2</sub>O to 5 psi:** to 1000 psi **15 to 1000 psi:** to 3000 psi **1500 to 5000 psi:** to 10,000 psi

Absolute/Barometric Pressure:

5 to 1000 psia: to 6000 psia **1500 to 5000 psia:** to 10,000 psia

#### Overpressure

#### Gage/Vacuum/Compound Pressure:

10 inH<sub>2</sub>O: 10 times span psi: 6 times span

**2.5 psi to 1000 psi:** 4 times span **1500 psi to 5000 psi:** 7250 psi maximum

Absolute/Barometric Pressure:

5 psia: 6 times span

15 psia to 1000 psia: 4 times span 1500 to 5000 psia: 7250 psia maximum

Wetted Parts: 316L stainless steel


Weight: 200 g (7 oz)

Operating Temperature Range: -40 to 85°C (-40 to 185°F)

**Compensated Temperature:** 

Ranges >5 psi: -29 to 85°C (-20 to 185°F) Ranges ≤5 psi: -17 to 85°C (0 to 185°F)





0 to 250 0 to 17.2 PX409-250GUSBH PX409-250AUSBH 0 to 500 0 to 34.5 PX409-500GUSBH PX409-500AUSBH 0 to 750 0 to 51.7 PX409-750GUSBH PX409-750AUSBH 0 to 1000 0 to 69 PX409-1.0KGUSBH PX409-1.0KAUSBH PX409-1.5KGUSBH 0 to 1500 0 to 103 PX409-1.5KAUSBH 0 to 2500 0 to 172 PX409-2.5KGUSBH PX409-2.5KAUSBH 0 to 3500 0 to 241 PX409-3.5KGUSBH **PX409-3.5KAUSBH** 0 to 5000 0 to 345 PX409-5.0KGUSBH PX409-5.0KAUSBH **VACUUM RANGES (NEGATIVE GAGE PRESSURE)** 0 to -10 inH<sub>2</sub>O PX409-10WVUSBH 0 to -25 mb 0 to -1 psi 0 to -69 mb PX409-001VUSBH 0 to -2.5 psi 0 to -172 mb PX409-2.5VUSBH 0 to -5 psi 0 to -345 mb PX409-005VUSBH 0 to -1 PX409-015VUSBH 0 to -15 psi **COMPOUND GAGE RANGES** PX409-10WCGUSBH ± 10 inH2O ± 25 mb PX409-001CGUSBH ± 1 psi ± 69 mb ± 2.5 psi ± 172 mb PX409-2.5CGUSBH ± 345 mb PX409-005CGUSBH ± 5 psi PX409-015CGUSBH ± 15 psi ± 1 **BAROMETRIC RANGES (ABSOLUTE PRESSURE)** PX409-32BUSBH 0 to 32 inHg 0 to 1100 mb 550 to 1100 mb **PX409-16BUSBH** 16 to 32 inHg 880 to 1100 mb PX409-26BUSBH 26 to 32 inHg Comes complete with 5-point NIST traceable calibration certificate, cable with USB connector, and free downloadable PC software.

Comes complete with 5-point NIST traceable calibration certificate, cable with USB connector, and free downloadable PC software. **Ordering Examples: PX409-100GUSBH,** 2 m (6') cable with USB termination, 100 psig range, USB output.

PX409-16BUSBH, 2 m (6') cable with USB termination, 16 to 32 inHg absolute barometric range, USB output.

## HIGH SPEED USB DIFFERENTIAL PRESSURE TRANSDUCERS

#### **SPECIFICATIONS DIFFERENTIAL MODELS**

Ranges: Unidirectional 10 inH2O to

1000 psi

Line/Static Pressure: 500 psi maximum applied to both sides simultaneously

**High Side Containment Pressure** (Differential)

Wet/Dry and Wet/Wet:

10 inH2O to 5 psi: to 1000 psi 15 to 1000 psi: to 3000 psi

#### **Overpressure (Differential)** Wet/Dry and Wet/Wet:

10 inH<sub>2</sub>O: 3.6 psi

1 psi: to 6 psi 2.5 psi to 750 psi: 4 times span

**1000 psi:** to 3000 psi Weight: 227 g (8 oz)

Line Pressure: 500 psi maximum

Fitting: 1/4-18 NPT male



RANGE		
psi	bar	MODEL NO.
WET/DRY DIFFERENTIAL	PRESSURE MODELS	
0 to 10 inH <sub>2</sub> O	0 to 25.00 mb	PX409-10WDDUUSBH
0 to 1	0 to 69.00 mb	PX409-001DDUUSBH
0 to 2.5	0 to 172.0 mb	PX409-2.5DDUUSBH
0 to 5	0 to 345.0 mb	PX409-005DDUUSBH
0 to 15	0 to 1.000	PX409-015DDUUSBH
0 to 30	0 to 2.100	PX409-030DDUUSBH
0 to 50	0 to 3.400	PX409-050DDUUSBH
0 to 100	0 to 6.900	PX409-100DDUUSBH
0 to 150	0 to 10.30	PX409-150DDUUSBH
0 to 250	0 to 17.20	PX409-250DDUUSBH
0 to 500	0 to 34.50	PX409-500DDUUSBH
0 to 750	0 to 51.70	PX409-750DDUUSBH
0 to 1000	0 to 69.00	PX409-1.0KDDUUSBH
WET/WET DIFFERENTIAL	PRESSURE MODELS	
0 to 10 inH <sub>2</sub> O	0 to 25.00 mb	PX409-10WDWUUSBI
0 to 1	0 to 69.00 mb	PX409-001DWUUSBH
0 to 2.5	0 to 172.0 mb	PX409-2.5DWUUSBH
0 to 5	0 to 345.0 mb	PX409-005DWUUSBH
0 to 15	0 to 1.000	PX409-015DWUUSBH
0 to 30	0 to 2.100	PX409-030DWUUSBH
0 to 50	0 to 3.400	PX409-050DWUUSBH
0 to 100	0 to 6.900	PX409-100DWUUSBH
0 to 150	0 to 10.30	PX409-150DWUUSBH
0 to 250	0 to 17.20	PX409-250DWUUSBH
0 to 500	0 to 34.50	PX409-500DWUUSBH
0 to 750	0 to 51.70	PX409-750DWUUSBH
0 to 1000	0 to 69.00	PX409-1.0KDWUUSBI

Comes complete with 5-point NIST traceable calibration certificate, cable with USB connector, and free downloadable PC software.

Ordering Examples: PX409-100DDUUSBH, Wet/Dry 0 to 100 psi differential high speed USB output transducer.

PX409-2.5DWUUSBH, Wet/Wet 0 to 2.5 psi differential high speed USB output transducer.

Over East Saust

### OMEGA USBH MAJOR SOFTWARE UPDATE


OMEGA is excited to announce the release of a major software update for USB Transducers! The fresh look and added features add even more value and flexibility to your transducer's performance. Free OMEGA PC software takes the data from the transducer directly to the digital domain, turning your laptop or Windows® tablet (with USB connection) into a virtual meter, chart recorder, or data logger. Also included are .NET APIs and a set for command-line access.

Visit ftp://ftp.omega.com/public/DASGroup/products/USBH/ to download your free copy.\*

\* Includes software to run TRH Central compatible devices.

Charting Window – The addition of a charting window allows you to see your data graphed in real time. The Y axis is configurable to allow simultaneous graphing of multiple engineering units. You can output the image of your data to a png file.





Channels Window – Display data from all of your sensors simultaneously. Each channel has configurable user alarms, three data filters, tare, resettable low/high indication, and sample rates ranging from 30 minutes to 1000 Hz.

Add

**Logging Window** – A new xls filetype output option presents preformatted data for readability. In addition, Live Statistics are displayed, including the sensor information, the start/stop time, the number of samples taken, the current reading, and the High/Low readings. With the logging window, you can capture your data for later analysis.

PX409-USBH-425117 Units psi Count 10 Last 14.2349 Low 14.2349 High 14.2353

Support for Omega Pressure, Force, Temperature, and Humidity USB Transducers One software package supports:

PX409-\*-USB, PX409-\*-USBH, LC411-\*-USBH, TJ-USB, IR-USB, RH-USB and UTC-USB transducers.











