High Temperature Blackbody Calibration



We make running changes when

technical advances allow. Check at time

of ordering for additional features.

Source

BLACK POINT™ BB-4A



Standard

- ✓ Calibrate From 100 to 982°C (212 to 1800°F)
- ✓ Portable Rugged Design
- ✓ Built-In Digital PID Autotune Temperature Controller with **Temperature Readout**
- ✓ NIST-Traceable **Calibration Certificate** Included with 3 Data Points
- ✓ RS232 Standard
- Built-In Type K Reference **Probe Output**

This BB-4A is a blackbody temperature reference source which is adjustable over the range from 100 to 982°C (212 to 1800°F) and accurate to \pm 1°C, \pm 0.25% reading of the indicated temperature. It has a built-in digital temperature controller to provide accurate, stable temperatures as well as to provide the temperature readings of the cavity. The heated cavity provides a target of known temperature and emissivity, and virtually any infrared pyrometer with a spot size diameter less than 22 mm (0.88") can be calibrated. The compact, portable design allows for quick and easy calibration setups.

Specifications

Operating Temperature Range:

100 to 982°C (212 to 1800°F) **Accuracy:** ±1°C, ±0.25% $(\pm 1.8^{\circ}F \pm 0.25\%) rdg$ Stability: ±0.15°C or less **Environmental Operating Conditions**

Ambient Temperature: 0 to 50°C (32 to 122°F)

Caution: To avoid fire hazard or damage to your calibrator, always allow your calibrator to cool down to ambient temperature before returning to storage.



Humidity: 0 to 90% RH non-condensing Power: 115 Vac, 50/60 Hz or

230 Vac, 50/60 Hz, 400 W **Internal Sensing Element:** Type K thermocouple Cavity Emissivity: 0.99 Warm-Up Time: 1.0 hr from ambient to 982°C (1800°F) Cavity Opening: 22 mm (0.88")

Weight:

BB-4A: 8 kg (17 lb)

BB-4A-230VAC: 15 kg (33 lb)

Dimensions:

190 H x 410 W x 264 mm D (7.5 x 16.12 x 10.4")

To Order	
Model No.	Description
BB-4A	High temperature blackbody, 115 Vac range 100 to 982°C (212 to 1800°F)
BB-4A-230VAC	High temperature blackbody, 230 Vac range 100 to 982°C (212 to 1800°F)

Comes complete with operator's manual and NIST calibration certificate. Ordering Examples: BB-4A, high-temperature blackbody calibration source.