

Microprocessor-Based Circular Chart Recorder

CT6100 Series



- ✓ Accepts Thermocouple, RTD, Vdc, and mA DC Inputs
- ✓ High Accuracy and Stability
- ✓ User Configurable via Front-Panel Keypad
- ✓ Easy-to-Use Menu-Driven Interface for Rapid Configuration and Calibration
- ✓ Available in 1-, 2-, or 3-Pen Versions
- ✓ Large-Character Alphanumeric LCD with Backlight
- ✓ Simultaneous Digital Display of Process Variable for Each Channel
- ✓ Programmable Locks for Security



CT6103 shown smaller than actual size.

The CT6100 Series microprocessor-based circular chart recorders are available in 1-, 2-, or 3-channel variants. They combine the simplicity and clarity of pen drawing with the versatility of microprocessor control. Each channel is compatible with all industry-standard sensors and signals, including thermocouple Types J, K, T, E, N, R, S, and B; Pt100 platinum RTDs; and 4 or 20 mA current loops.

Low and high measurement ranges are provided for each input type; separate range cards are not required. Multi-input versions feature optoelectronic isolation of the input stages to eliminate troublesome installation ground loops. Multislope integrating 16-bit A/D converters ensure precise measurement by sampling the input every 0.5 seconds.

Thermocouple and RTD characteristics are fully linearized. The recorders use automatic cold-junction compensation for thermocouple measurement.


All CT6100 Series models feature alarm relays. Single-pen recorders are equipped with 3 fail-safe single-pole changeover relays; 6 relays are standard on the 2- and 3-pen versions. Color-coded LEDs indicate the status of each relay. All relay functions are user selectable; setpoint values and hysteresis levels are entered directly via the keypad, while relay action and channel assignment are selected from user-friendly menus. Circuit precision is matched by the backlash-free pen-drive mechanism, which has a positioning resolution

greater than 0.1%. An integral feedback potentiometer enables closed-loop monitoring of each pen position.

Each recorder uses a low-maintenance stepper motor. The rotation speed of the 244 mm diameter chart is microprocessor controlled and user programmable.

All CT6100 recorders are housed in a strong molded case that can be panel or surface mounted. A gasket-lockable door protects internal components from harsh industrial environments and offers protection rated to NEMA 12 (IP55). A tough acrylic window lets the user view the chart trace, digital channel readings, and alarm status with the recorder's door closed.

Don't Forget to Order Additional Recorder Paper!



Specifications

Inputs

Input Types: Thermocouple K, T, J, N, E, B, R, S; Platinum RTD (Pt100) 3-wire; $\pm 2V$, $+20Vdc$; $\pm 2mA$, $\pm 20mA$

Input Ranges: Thermocouples to BS4937 (type B minimum temp 200°C); RTD to BS1904:1984

Cold Junction Compensation: Automatic; $\pm 0.02^\circ C/^\circ C$ stability

Input Resistance:

Thermocouple: 10 M Ω

$\pm 2mA$: 200 Ω

$\pm 20mA$: 20 Ω

$\pm 2V$, $\pm 20V$: $>1M\Omega$

Min Span: 5°C (9°F), thermocouples K, J, T, E, N and RTD; 50°C (90°F) other thermocouple types, 50 mV, 200 mA

T/C BURN-OUT: Pull-up or pull-down, selectable

RTD Lead Resistance:

3-wire, compensated up to 10 Ω maximum per lead

Input Protection: $\pm 50Vdc$ on signal inputs

Input Isolation: Optoelectronic on 2 and 3 input models 500 Vrms channel-to-channel, 500 Vrms channel-to-ground

Sensor/Transmitter Power:

12 or 24 Vdc, 25 mA, selectable; for current loop inputs

Performance

Accuracy:

RTD, Low Range (-200 to 200°C): $\pm 0.2^\circ C$

RTD, High Range (200 to 850°C): $\pm 0.8^\circ C$

Thermocouple: $\pm 0.25\%$ full scale

Voltage/Current: $\pm 0.2\%$ full scale

Temperature Stability:

$\pm 0.02\%$ FS/ $^\circ C$

Linearization Accuracy:

T/C Types J, K, T, N, E: $\pm 0.1^\circ C$,

-50 to 200°C, $\pm 1^\circ C$ maximum

T/C Types R and S: $\pm 0.2^\circ C$,

-50 to 200°C, $\pm 1^\circ C$ maximum

T/C Type B: $\pm 1^\circ C$ maximum

RTD: $\pm 0.1^\circ C$, -200 to 850°C

Calibration Shift: $\pm 10^\circ C$ user programmable to eliminate sensor errors (thermocouple and RTD)

Chart and Display

Chart Size: 244 mm (9.6") diameter;

40, 50, 60, 70 or 80 linear divisions

Chart Drive: DC stepper motor

Chart Speeds: 1 to 24 hours in steps of one hour, 2 to 31 days in steps of 1 day

Writing Method: Disposable ink cartridges; pen 1-red; pen 2-green; pen 3-blue

Pen Positioner: DC stepper motor

Positioning Resolution:

$>0.1\%$ full scale

Response Time:

Zero to full scale in 4.5 seconds

Pen Lift: Powered, activated from front panel; chart fast time advance possible with pens raised

Display: 2 line x 20 character dot matrix liquid crystal with backlight and automatic temperature compensation; 9.6 mm (0.37") character height

Display Resolution:

0.1°C for temperature inputs, software programmable for voltage/ current inputs

Alarm Display: Relay status shown by red and green front panel LEDs

Relays

Type: SPDT; 30 Vdc or 250 Vac @ 6 A maximum; 150 W DC, 1660 Vac non-inductive

Action: Software selectable from: high alarm/low alarm/deviation alarm/control relay (high)/control relay (low); relays de-energize in alarm state; assignable to any channel

Hysteresis: User programmable 0.0 to 10% span

Snubber Network: 22 nF and 100 Ω across each contact

Analog Output (Option)

Type: 0 to 20/4 to 20 mA; assignable to any channel; range selectable within any segment of chart range

Resolution: 12-bit

Compliance: 20V approx

Isolation: Optoelectronic

Action: direct or reverse

General

Security: 3-level software lock including password protection, internal hardware jumper lock, lockable door

Power: 115 or 230 Vac $\pm 10\%$, switch selectable, 50/60 Hz: terminal block connection

Power Requirements: $<25W$

Operating Ambient: 0 to 55°C

(32 to 131°F), 0 to 90% RH

(non condensing)

Case: Steel, with glass-filled polyester resin door with acrylic window

Protection: NEMA 12 (IP55)

Mounting: Panel or surface

Dimensions: 336 W x 396 H x 171 mm D (13.2 x 15.6 x 6.7")

Weight: From single pen: 7 kg (15.4 lb) to three pen: 7.7 kg (17.0 lb)

Panel Cutout: 288 W x 356 mm H (11.3 x 14.0")



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

To Order Visit omega.com/ct6100 for Pricing and Details

Model No.	Description
CT6101	1-pen recorder with 3 relays and transmitter power supply
CT6102	2-pen recorder with 6 relays and transmitter power supply
CT6103	3-pen recorder with 6 relays and transmitter power supply

Accessories

Model No.	Description
CT6100-RED	Red pens, pack of 3
CT6100-GREEN	Green pens, pack of 3
CT6100-BLUE	Blue pens, pack of 3
CT6100-0-100/24H	100 chart papers, 24 hours
CT6100-0-100-31D	100 chart papers, 31 days
POWERCORD-SE	Power cord with one end stripped

Option*

Order Suffix	Description
-PV	Analog output of 0 to 20 mA or 4 to 20 mA, assignable to any channel

* Option is not field installable. It must be ordered at the time of purchase.

Comes complete with 1 package of 24 hour chart paper, pen(s) and operator's manual.

Ordering Example: CT6101, 1-pen recorder with 3 relays and transmitter power supply and POWERCORD-SE, power cord.

OCW-3, OMEGACARESM extends standard 1-year warranty to a total of 4 years.