



INDUSTRIAL pH INSTRUMENTATION & ELECTRONICS

Microprocessor-Based pH and Temperature Recorders with Large, 200 mm (8") Diameter Charts


CTPH
\$970



Electronics Only 220 V Model Only

- ✓ Ranges: 0.2 to 12.0 pH; 2 to 80°C (36 to 176°F)
- ✓ In-Line or Submersible pH Sensor with PPS (Ryton®) Body and 3/4 NPT
- ✓ 120 Double-Sided Circular Charts: 1-, 7-, 32-Day Records
- ✓ Alarm Contact
- ✓ Benchtop or Wall Mounted
- ✓ Battery or AC Power
- ✓ LCD Backlight and Chart Light (with AC Power)
- ✓ Audible Alarm

The CTPH is a cost-effective recorder for pH and temperature. The pH range is 0.2 to 12.0 with automatic temperature compensation. An electronically amplified probe provides pH and temperature input to the recorder through a 6-pin mini DIN connector.



Sensor included, order CTPH-PROBE, \$225, for replacement



PATENTED

Covered by U.S. and International patents and pending applications

AVAILABLE FOR FAST DELIVERY!

Specifications

pH Input (Green Pen)

pH Range: 0.2 to 12.0 pH
Resolution: 0.1 pH on LCD and 0.2 pH on chart

Accuracy: ± 0.2 pH

ATC Range: 0 to 80°C (32 to 176°F)

Sensor: In-line or submersible PPS (Ryton®) body with 3/4 MNPT, sealed double-junction PFA and a pre-amplified output to ensure accurate signal over long distances

Cable Length: 1.8 m (6')

Temperature Input (Red Pen)

Temperature Range: 0 to 100°C (32 to 212°F)

Resolution:

1°C on LCD and 2°C on chart

Accuracy: ±2°C (±10°F)

Sensor: pH and temperature

Display: User switchable

Chart: 200 mm (8") circular linear radial divisions. 1-, 7-, 32-day, with pH and °C scale

Dimensions: 33.5 H x 27.1 W

x 6.7 cm D (13³/₁₆ x 10¹¹/₁₆ x 2⁵/₈"

Weight: Approx. 3.2 kg (7 lb) with batteries

To Order (Specify Model Number)

Model No.	Price	Description
CTPH-110V-G-AL	\$970	Recorder, 110 Vac
CTPH-220V-G-AL	970	Recorder, 220 Vac
CT585-PS	10	Red (temp) and green (pH) pen set
CT585-PS-6	52	Package of 6 pen sets
CTPH-C(*)C	19	100 double-sided charts
CTPH-BNC	99	BNC pH adaptor
CTPH-PROBE	225	Replacement pH probe

Comes in a charcoal gray color, with detachable solid state pH/temperature sensor, additional 1.8 m (6') extension cable, 120 double-sided charts (40 each of 1-day, 7-day and 32-day, all °C), two sets of pens, wall-mount template and hardware, 110 or 220 Vac adaptor, chart lights, 4 "D" alkaline batteries and complete operator's manual.

*Insert "D" for 1 day, "W" for 7 days, "M" for 32 days of recording (all charts are °C).

For white case, replace "-G" with "-W", no additional charge.

Note: With the BNC adaptor, the ATC is disabled and any low-cost pH sensor can be used, such as PHE-4202, \$65.

Ordering Example: CTPH-110V-G-AL recorder, CTPH-CDC, pack of 100 double-sided 1-day charts, \$970 + 19 = \$989. OCW-3 OMEGACARESM extends standard 1-year warranty to a total of 4 years, \$242, \$970 + 242 = \$1212. OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters