

Compact Digital Multimeters

With Non-Contact Voltage Detection



HHM-MN42/
HHM-MN47



- ✓ 0.5% Basic Accuracy
- ✓ Over-Sized High Contrast LCD
- ✓ Double Molded Housing
- ✓ CAT III-600V
- HHM-MN42**
- ✓ Manual Ranging
- ✓ 2000 Count Display
- ✓ 1.5 and 9V Battery Tests
- HHM-MN47**
- ✓ Autoranging with Manual Override
- ✓ 4000 Count Display
- ✓ AC Current, Capacitance, Frequency, Temperature, and Duty Cycle
- ✓ Relative and Data Hold Functions



HHM-MN42



HHM-MN47

All models shown smaller than actual size.

The HHM-MN42 and HHM-MN47 multimeters have a non-contact voltage detector which quickly checks for the presence of voltage from 100 to 600 Vac.



Free Thermocouple Included!

These models include a free 1 m (40") Type K insulated beaded wire thermocouple with subminiature connector and wire spool caddy (1 per channel). **Order a Spare!**
Model No. SC-GG-K-30-36

Specifications	HHM-MN42	HHM-MN47
Ranging	Manual	Autoranging
Display Counts	2000	4000
Basic Accuracy	0.5%	0.5%
NC Voltage Detector	100 to 600 Vac	100 to 600 Vac
DC Voltage	600V (0.1 mV)	600V (0.1 mV)
AC Voltage	600V (0.1V)	600V (0.1 mV)
DC Current	10A (1 μ A)	10A (0.1 μ A)
AC Current	—	10A (0.1 μ A)
Resistance	2M Ω (0.1 Ω)	40M Ω (0.1 Ω)
Capacitance	—	100 μ F (1pF)
Frequency	—	10 MHz (0.001 Hz)
Temperature	—	760°C (1400°F)
Duty Cycle	—	0.1 to 99.9%
Diode/Continuity	Yes	Yes
Battery Test	1.5V / 9V	—
Dimensions	150 x 70 x 48 mm (5.9 x 2.75 x 1.8")	150 x 70 x 48 mm (5.9 x 2.75 x 1.8")
Weight	255 g (9 oz)	255 g (9 oz)
Power	9V battery included	9V battery included

To Order Visit omega.com/hhm-mn42_47 for Pricing and Details

Model No.	Description
HHM-MN42	Manual ranging multimeter and voltage detector
HHM-MN47	Autoranging multimeter with temp and voltage detector

Comes complete with test leads, Type K bead wire probe for HHM-MN47, 9V battery, carrying case and operators manual.
Ordering Example: HHM-MN42, manual ranging multimeter and voltage detector.

