3-Prong Miniature ConnectorsFor Thermocouples, RTD's and 3-Wire Thermistors

MTP Series

- Supplied with Shielded Wire **Copper Connection Pin**
- Heavy Duty Construction
- Color-Coded
- Accepts Stranded or Solid Wire up to Size 20 AWG
- Combination Phillips/ Slot Screws
- ✓ Glass-Filled Nylon Rated from -29 to 180°C (-20 to 356°F)






Miniature uncompensated version male and female shown actual size.

> Maximum wire diameter is 3 mm (0.125").

For OMEGA's **Selection of Connector Accessories** Visit Us Online

We make running changes when technical advances allow. Check at time of ordering for additional features.

Note: Minor discoloration of connector may occur between 150°C (302°F) and 180°C (356°F). Electrical properties are not affected.



Discount Schedule	
1-10	Net
11-49	5%
50-99	10%
100-999	15%
1000-4999	20%
5000 and over	25%



To Order								
	Type of Thermocouple	Compensating Alloy Used in Connector			Model No. ANSI			
Alloy Code†	Used with Connector	+	_	G	Shell Color	Color Code		
K	CHROMEGA®-ALOMEGA®	CHROMEGA	ALOMEGA	Copper	Yellow	MTP-K-(*)		
T	Copper-Constantan	Copper	Constantan	Copper	Blue	MTP-T-(*)		
J	Iron-Constantan	Iron	Constantan	Copper	Black	MTP-J-(*)		
E	CHROMEGA-Constantan	CHROMEGA	Constantan	Copper	Purple	MTP-E-(*)		
U	Uncompensated	Copper	Copper	Copper	White	MTP-U-(*)		
N	OMEGALLOY®	OMEGA-P®	OMEGA-N®	Copper	Orange	MTP-N-(*)		

† K, T, J, E, R, S and B are ANSI designations.
*To order, specify "M" for male connector only, or "F" for female connector only.

OMEGALLOY Type N is generically known as Nicrosil-Nisil.

OMEGA's subminiature connectors are molded of high performance glass-filled nylon. Connectors will accommodate protection tubes from 0.25 mm to 3.17 mm (0.010" to 1/6") O.D. Bushings can be purchased for an additional cost; order BB-SMP-1.