

Thermocouple Assembly Kit

- ✓ Build Micro-Miniature, Standard or Heavy-Duty Thermocouples
- ✓ Provides Cryogenic Through High Temperature Service
- ✓ Create Assemblies in Minutes
- ✓ Contains 4 Thermocouple Types
- ✓ Carrying Storage Case Included

N-965
Complete Kit
with Instructions



Note: The contents of this kit can be purchased separately if desired. However, there is a significant cost savings to purchase the complete kit.

NOW AVAILABLE
At no extra charge, the OMEGA N-965 can be supplied in 1 or 2 thermocouple combinations instead of an assortment. Specify which combinations you desire.

Contents

- | | |
|--|---|
| <ul style="list-style-type: none"> 12 Color-coded connectors (male and female)— 3 each: CHROME[®]GA-ALOME[®]GA, Iron-Constantan, Copper-Constantan and CHROME[®]GA-Constantan 12 Tube clamps— 3 each: 1/16, 1/8, 3/16 and 1/4" sizes 12 Cable clamps 12 Compression fittings— 3 each: 1/16, 1/8, 3/16 and 1/4" sizes 8 Inconel, closed-end tubes—6" length 2 each: 1/16, 1/8, 3/16 and 1/4" OD 8 Stainless steel closed-end tubes—6" length 2 each: 1/16, 1/8, 3/16 and 1/4" OD 4 Inconel open-end tubes—6" length 1 each: 1/16, 1/8, 3/16 and 1/4" OD 4 Stainless steel open-end tubes—6" length 1 each: 1/16, 1/8, 3/16 and 1/4" OD 24 Two-hole insulating tubes—6" length 6 each: 3/4, 1/2, 1/4 and 3/16" OD 2 Containers CC cement (1 oz) | <ul style="list-style-type: none"> 60 Thermocouples—12" leads 5 each CHROME[®]GA-ALOME[®]GA 0.005" 5 each CHROME[®]GA-ALOME[®]GA 0.015" 5 each CHROME[®]GA-ALOME[®]GA 0.032" 5 each Iron-Constantan 0.005" 5 each Iron-Constantan 0.015" 5 each Iron-Constantan 0.032" 5 each Copper-Constantan 0.005" 5 each Copper-Constantan 0.015" 5 each Copper-Constantan 0.032" 5 each CHROME[®]GA-Constantan 0.005" 5 each CHROME[®]GA-Constantan 0.015" 5 each CHROME[®]GA-Constantan 0.032" 7.6 m (25') CHROME[®]GA-ALOME[®]GA 20 AWG extension wire 7.6 m (25') CHROME[®]GA-Constantan 20 AWG extension wire 7.6 m (25') Copper-Constantan 20 AWG extension wire 7.6 m (25') Iron-Constantan 20 AWG extension wire |
|--|---|