1/16 DIN Multi-Programmable Timers **OF OMEGA**

PTC-20 Series



- ✓ ¼ DIN Cutout
- **✓** 3 Different Models:
 - Standard
 - High-Performance
 - Repeat Cycle
- ✓ 4-Digit Dual-Line Display Indicates Set Value and Time Value
- **✓** All Models Offer Multiple Field-Programmable **Modes For Operation** and Time Ranges
- ✓ NEMA 4 (IP65) Rated for Use in Washdown Conditions
- Universal AC Supply Voltage (90 to 264 Vac)
- ✓ 5 A Relay Output or **Open-Collector Output**
- ✓ Industry-Standard 11-Pin Socket Connection*

If you are looking to outfit your control panel with timers that have an attractive LED display, consider the PTC-20 Series, which delivers functionality at competitive prices.

Designed to fit the correct timer to your application, the PTC-20 Series comprises 3 models. The PTC-21 base unit offers 5 field-selectable operating modes and time ranges as well as a host of other convenient features. The high-performance PTC-23 offers advanced functions. such as dual setpoints and 1 ms resolution. The PTC-22 provides a repeat cycle (batch stop, batch continue) and interval modes specifically tailored for cyclical operations.

General Specifications

Supply Voltage: 90 to 240 Vac,

50/60 Hz

Power Consumption: <10 VA

Resolution: Settable for time values in hours/minutes/seconds ranges

Inputs Start and Reset: NPN or dry

contact

Activation Time: 21 ms (85 to 264 Vac

powered units)





PTC-22

All models shown smaller than actual size.

Impedance: 10 kΩ

Available, Visit OMEGA

Front-Panel Rating: IEC IP65 Operating Temperature: 0 to 55°C

(32 to 131°F)

Storage Temperature: -40 to 90°C

(-40 to 194°F)

Humidity: 5 to 95% RH, non-condensing

PTC-23

Memory: Non-volatile

Operation

Time Ranges: Hours, minutes, seconds; hours, minutes; minutes, seconds Repeat Accuracy: ±0.01%

Physical

Dimensions: 48 H x 48 W x 85 mm D

(1.89 x 1.89 x 3.35")

Display: Dual-line, 4-digit, 7-segment

LED, 8 mm H (0.31")

Mounting: Panel-mount 45 x 45 mm (1.77 x 1.77"), cutout or DIN rail Wiring Connection: Screw terminals on an 11-pin socket

Weight: 100 g (3.5 oz) Base Model PTC-21

Output: Timed relay, DPDT (5 A) Operating Modes (Shown): On-delay, off-delay, on-delay (interval), interval

and repeat cycle

Repeat Cycle PTC-22

Inhibit: NPN or dry contact

Outputs:

Relay: 2 SPDT (5 A), 15 ms latency

Transistor: NPN

Open Collector: 30 Vdc, 30 mA max

Operating Mode (Shown): Repeat Cycle: Batch stop, batch

continue and interval

High Performance PTC-23

Inhibit: NPN or dry contact

Outputs:

Relay: 2 SPDT (5 A), 15 ms max latency

Transistor:

NPN Open Collector: 30 Vdc, 30 mA max opto isolated Operating Modes: 17 different operating modes available (popular

modes shown)



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

To Order	
Model No.	Description
PTC-21	Standard timer
PTC-22	Repeat-cycle timer
PTC-23	High-performance timer
PTC-21-SOCKET	Socket for PTC-20 Series - *Required for operation

Comes complete with operator's manual. Ordering Example: PTC-21, standard timer.

OCW-2, OMEGACARE™ extends standard 1-year warranty to a total of 3 years.