

Ordering Examples: RTD-3-F3105-36-G, 100 Ω, 2 x 2 mm, thin film Pt100 RTD element, Class A accuracy with 4-wire fiberglass insulated cable 1 m (40") long with ceramic cement over connection and stripped leads.

RTD-2-1PT100KN2515-36-G-MTP, 100 Q, 1.5 Dia. x 25 long mm, Pt100 wire wound element, Class A accuracy with 3-wire fiberglass insulated cable 1 m (40") long with ceramic cement over connection and miniature 3-pin connector.



RTD Sensors— Fast Response Exposed RTD Element with PFA Lead Wires



C

Thermal Response (63%) Less Than 1 Second

- High Accuracy Class A, Pt100 and Pt1000 RTD Elements Standard
- Higher Accuracy ½ and ½ DIN Elements Are Available in Some Styles*
- Operating Range: -30 to 260°C (-22 to 500°F) Class A Thin Film Element Styles, -100 to 260°C (-148 to 500°F) Class A Wire Wound Element Styles
- 1 m (40") Long 2-, 3- or 4-Conductor #26 AWG Stranded Nickel Plated Copper, PFA Insulated and Jacketed Cable Constructions Available
- Epoxy Potting Insulating Element to Cable Connection

* **Note:** Temperature range for $\frac{1}{3}$ DIN is 0 to 150°C (32 to 302°F) and temperature range for $\frac{1}{3}$ DIN is 0 to 100°C (32 to 212°F). Also, note 4-wire configuration only for $\frac{1}{3}$ DIN.

Image: Construction of the construction of

shown actual size.


To Order				
Model No.	Resistance at 0° and Accuracy	Element Size	Element Type	
RTD-2-F3105-36-T	100 ±0.06 Ω , Class A	2 W x 2 mm L	Thin film	
RTD-2-F3102-36-T	100 ±0.06 Ω, Class A	4 W x 5 mm L	Thin film	
RTD-2-1PT100KN2515-36-T	100 ±0.06 Ω, Class A	1.5 Dia. x 25 mm L	Wire wound	
RTD-2-1PT100KN2528-36-T	100 ±0.06 Ω, Class A	2.8 Dia. x 25 mm L	Wire wound	
RTD-2-F3145-36-T	1000 ±0.60 Ω, Class A	2 W x 2 mm L	Thin film	
RTD-2-F3142-36-T	1000 ±0.60 Ω, Class B	4 W x 5 mm L	Thin film	

For 2-wire, replace "2" in model number with "1" and subtract cost from price. For 4-wire assembly, replace "2" in model number with "3" and add cost to price. For ½ DIN accuracy, add "-1/3" to end of model number for additional cost. For ½ DIN accuracy, add "-1/10" to the model number for additional cost. For ½ DIN accuracy, add "-1/10" to the model number for additional cost. (Note: ½ DIN option is only available in 4-wire construction). For longer leads, change "36" in model number to length in inches and add cost for 3- and 4-wire cables, or 2-wire cables, for an additional cost. For spade style terminal lugs standard termination in stripped leads, add "-LUG" to the model number for additional cost. For connectors (3-wire only) add "-OTP" to the model number for additional cost.

Ordering Examples: RTD-3-F3105-36-T-1/3, 100 Ω , 2 x 2 mm, thin film Pt100 RTD element, ½ DIN accuracy with 4-wire PFA insulated cable 1 m (40") long with epoxy over connection and stripped leads.

RTD-2-1PT100KN2515-36-T-MTP, 100 Ω , 1.5 Dia. x 25 long mm, Pt100 wire wound element, Class A accuracy with 3-wire PFA insulated cable 1 m (40") long with epoxy over connection and miniature 3-pin connector.






To Order

Model No.	Resistance at 0° and Accuracy	Element Size	Element Type	
RTD-2-F3105-36-B	100 ±0.06 Ω , Class A	2 W x 2 mm L	Thin film	
RTD-2-F3102-36-B	100 ±0.06 Ω, Class A	4 W x 5 mm L	Thin film	
RTD-2-1PT100KN2515-36-B	100 ±0.06 Ω, Class A	1.5 Dia. x 25 mm L	Wire wound	
RTD-2-1PT100KN2528-36-B	100 ±0.06 Ω, Class A	2.8 Dia. x 25 mm L	Wire wound	
RTD-2-F3145-36-B	1000 ±0.60 Ω, Class A	2 W x 2 mm L	Thin film	
RTD-2-F3142-36-B	1000 ±0.60 Ω, Class B	4 W x 5 mm L	Thin film	

For 2-wire, replace "2" in model number with "1" and subtract cost from price. For 4-wire assembly, replace "2" in model number with "3" and add cost to price. For longer leads, change "-36" in model number to length in inches and add cost for 3- and 4-wire cables or 2-wire cables for additional cost.

Ordering Examples: RTD-3-F3105-36-B, 100 Ω , 2 x 2 mm, thin film Pt100 RTD element, Class A accuracy with 4-wire bare conductors, 1 m (40") long with no ceramic cement over connection and stripped leads.

RTD-2-1PT100KN2515-36-B, 100 Ω , 1.5 Dia. x 25 long mm, Pt100 wire wound element, Class A accuracy with 3-wire bare conductors, 1 m (40") long with no ceramic cement over connection.



FBGS-N-24 fiberglass sleeving.



OM-CP-OCTRTD data logger.



FRX-02018 thermocouple insulators.

