Most Popular Miniature OF OMEGA

Connectors Type SMPW Glass Filled Nylon -29 to 180°C (-20 to 356°F) Service Temperature Type HMPW Liquid Crystal Polymer -29 to 260°C (-20 to 500°F) Service Temperature

HMPW/SMPW

- Heavy Duty Construction
- ✓ Color-Coded for ANSI and IEC
- ✓ Captive Cover Screws
- Accepts Stranded or Solid Wire up to Size 20 AWG
- Quick Connect Contact Washers
- ✓ Internal Wire Divider
- Combination Phillips/Slot Screws
- ✓ Type HMPW Environmentally Friendly Cadmium-Free





SMPW — Glass-Filled Nylon HMPW — Cadmium Free Liquid Crystal Polymer

Shown smaller than actual size.

Note: SMPW only. Minor discoloration of connector may occur between 150°C (302°F) and 180°C (356°F). Electrical properties are not affected.

We make running changes when technical advances allow. Check at time of ordering for additional features.






For OMEGA's
Selection of Connector
Accessories
Visit Us Online

Available in sizes to fit 0.020

to 0.125" and 1.5 and 3.0 mm

diameter probes, visit us online.








Quick connect contact washers. Additional washers available, order CW-SMP-20, pkg of 20, or CW-SMP-100, pkg of 100





| To Order | | | | | |
|----------------|--|------------|----------------|---|---|
| Alloy Code† | Compensating Alloy Used in Connector + | | Shell Color | Glass-Filled Nylon Model Number w/Window | Liquid Crystal Polymer Model Number w/Window |
| K | CHROMEGA® | ALOMEGA® | Yellow | SMPW-K-(*) | HMPW-K-(*) |
| Ť | Copper | Constantan | Blue | SMPW-T-(*) | HMPW-T-(*) |
| J | Iron | Constantan | Black | SMPW-J-(*) | HMPW-J-(*) |
| E | CHROMEGA | Constantan | Purple | SMPW-E-(*) | HMPW-E-(*) |
| R/S | Copper | RNX/SNX | Green | SMPW-R/S-(*) | HMPW-R/S-(*) |
| Ğ | GPX | GNX | Red/Grn | SMPW-G-(*) | HMPW-G-(*) |
| C | CPX | CNX | Red | SMPW-C-(*) | HMPW-C-(*) |
| D | DPX | DNX | Red/Wht | SMPW-D-(*) | HMPW-D-(*) |
| U | Copper | Copper | White | SMPW-U-(*) | HMPW-U-(*) |
| N | OMEGA-P® | OMEGA-N® | Orange | SMPW-N-(*) | HMPW-N-(*) |

Ordering Examples: SMPW-K-M, glass-filled nylon, Type K male connector. SMPW-K-F, glass-filled nylon, Type K female connector.

^{*}To order, specify "M" for male connector only, or "F" for female connector only.
†J, K, T, E, R, S and B are ANSI designations. OMEGALLOY® is generically known as Nicrosil-Nisil. ANSI color coded models shown. Note: Non-Window models available, please consult Sales for details.

Type U (uncompensated) connectors are used with Type B thermocouples (Pt/6%Rh-Pt/30%Rh).